

PRODUCT INFORMATION PACKET

Model No: 132653.00

Catalog No: 132653.00

132653.00..7HP..NONE.184TZ.TENV.NONE.3PH.....

Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications


Output HP	NONE Hp	Output KW	5.2 kW
Frequency	NONE Hz	Voltage	NONE V
Current	NONE A	Service Factor	1
Phase	3	Duty	Continuous
Insulation Class	F	Design Code	NO DESIGN CODE
KVA Code	NONE	Frame	184TZ
Enclosure	Totally Enclosed Non Ventilated	Thermal Protection	No Protection
Ambient Temperature	40 °C	Drive End Bearing Size	NONE
Opp Drive End Bearing Size	NONE	UL	No
CSA	N	CE	N
IP Code	43	Number of Speeds	1


Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Rigid Base	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Assembly/Box Mounting	F1 ONLY
Outline Drawing	036338-1100	Connection Drawing	TBD

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/01/2022

036338



				TOLERANCES UNLESS SPECIFIED		 Regal Beloit America, Inc.	DRAWN MVG 07/13/2017		
				DEC.	INCHES		CHK	GR	07/13/2017
				.X	±.1		APPD	GR	07/13/2017
				.XX	±.03		SCALE 1=4		
				.XXX	±.005		REF OL132185		
A	NEW DRAWING	MVG 07/13/17	GR	.XXXX	±.0005	TITLE	OUTLINE 184T FRAME		
							T.E.N.V. - PARTIAL MOTOR		
						MAT'L.	FMF		
NO.	REVISION	BY & DATE	CHK	ANG	±1/2'	FINISH	PREV OLPR090002		
				RFP		CAD FILE	036338	SIZE	DRAWING NO. PAGE OF REV.
				DIST				A	036338 A

THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED
THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT