

Nameplate Specifications

Output HP	2 Hp	Output KW	1.5 kW
Frequency	60 Hz	Voltage	208-230/460 V
Current	8.8/4.4 A	Speed	860 rpm
Service Factor	1.15	Phase	3
Efficiency	78.5 %	Power Factor	54
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	J
Frame	213T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6207	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	8	Rotation	Reversible
Resistance Main	1.65 Ohms	Mounting	Rigid Base
Motor Orientation	Nan	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	NAN
Connection Drawing	005010.01	Outline Drawing	037599-1050

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:07/18/2022