



Nameplate Specifications

Phase	3	Output HP	7.60 & 2.20 Hp
Output KW	5.7 & 1.6 kW	Voltage	480 & 480 V
Speed	1750 & 1140 rpm	Service Factor	1.1 & 1.10
Frame	215TZ	Enclosure	Totally Enclosed Air Over
Thermal Protection	Thermostat	Ambient Temperature	70 °C
Frequency	60 & 60 Hz	Current	10 & 4.2 A
Duty	Continuous	Insulation Class	H
Design Code	NO DESIGN CODE	KVA Code	J
Drive End Bearing Size	6209	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	3.5 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Shaft Diameter	1.125 in
Assembly/Box Mounting	F1 ONLY		
Outline Drawing	OL140537	Connection Drawing	00504608

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/23/2023