



Nameplate Specifications

Phase	3	Output HP	10 & 15 Hp
Output KW	7.5 & 11.2 kW	Voltage	208-220/440 & 208-220/440 V
Speed	3470 & 3385 r/min	Service Factor	1.5 & 1.0
Frame	215TZ	Enclosure	Drip Proof
Thermal Protection	Thermostat	Efficiency	85.5 & 81.5 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	28-26/13 & 42-40/20 A	Power Factor	87
Duty	Continuous	Insulation Class	B
Design Code	B	KVA Code	G
Drive End Bearing Size	307	Opp Drive End Bearing Size	206
UL	Recognized	CSA	Y
CE	N	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Resistance Main	1.8 O	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Overall Length	17.41 in
Frame Length	11.15 in	Shaft Diameter	1.125 in
Shaft Extension	3.59 in	Assembly/Box Mounting	F3
Outline Drawing	037963-1115	Connection Drawing	A-EE7308T-LE