



Nameplate Specifications

Phase	1	Output HP	10 Hp
Output KW	7.5 kW	Voltage	230 V
Speed	1730 r/min	Service Factor	1.15
Frame	215TVZ	Enclosure	Drip Proof Air Over
Thermal Protection	No Protection	Efficiency	82.5 %
Ambient Temperature	80 °C	Frequency	60 Hz
Current	44.0 A	Power Factor	89
Duty	Continuous	Insulation Class	H
Design Code	L	KVA Code	G
Drive End Bearing Size	6307	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	N	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Resistance Main	0 O	Mounting	Rigid Base
Motor Orientation	Shaft Up	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Overall Length	20.65 in
Frame Length	12.40 in	Shaft Diameter	1.375 in
Shaft Extension	3.38 in	Assembly/Box Mounting	F1 ONLY
Connection Drawing	EE9048MF-LE	Outline Drawing	SS89636LE-1240