

Nameplate Specifications

| | | | |
|------------------------|----------------|----------------------------|------------|
| Output HP | 7.50 Hp | Output KW | 5.6 kW |
| Frequency | 60 Hz | Voltage | 230 V |
| Current | 36.0 A | Speed | 1740 rpm |
| Service Factor | 1.15 | Phase | 1 |
| Efficiency | 81.5 % | Power Factor | 83 |
| Duty | Continuous | Insulation Class | F |
| Design Code | NO DESIGN CODE | KVA Code | G |
| Frame | 213T | Enclosure | Drip Proof |
| Thermal Protection | Thermostat | Ambient Temperature | 40 °C |
| Drive End Bearing Size | 6209 | Opp Drive End Bearing Size | 6206 |
| UL | Recognized | CSA | Y |
| CE | N | IP Code | 22 |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|-------------------------------|--------------------|----------------------------|
| Electrical Type | Capacitor Start Induction Run | Starting Method | Across The Line |
| Poles | 4 | Rotation | Selective Counterclockwise |
| Resistance Main | .22 Ohms | Mounting | Rigid Base |
| Motor Orientation | Horizontal | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | T | Shaft Diameter | 3.255 in |
| Assembly/Box Mounting | F1 ONLY | | |
| Outline Drawing | OL141140 | Connection Drawing | 005077.11 |