



**Nameplate Specifications**

Phase	3	Output HP	10 & 15 Hp
Output KW	7.5 & 11.2 kW	Voltage	230/460 & 230/460 V
Speed	1745 & 1745 rpm	Service Factor	1.0 & 1.0
Frame	215TZ	Enclosure	Drip Proof Air Over
Thermal Protection	No Protection	Efficiency	87.5 & 87.5 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	39/19.6 & 39/19.6 A	Power Factor	81.3
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Drive End Bearing Size	6307	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	1		

**Technical Specifications**

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Resistance Main	.881 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Assembly/Box Mounting	F3
Outline Drawing	038095-1240	Connection Drawing	EE7308