



### Nameplate Specifications

Phase	3	Output HP	15 & 15 Hp
Output KW	11.2 & 11.2 kW	Voltage	230/460 & 190/380 V
Speed	1680 & 1345 rpm	Service Factor	1.25 & 1.0
Frame	215TCZ	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	No Protection	Efficiency	82.6 & 79.5 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	38/19 & 47/23.5 A	Power Factor	88.5
Duty	30 Minute	Insulation Class	H
Design Code	A	KVA Code	G
Drive End Bearing Size	6309	Opp Drive End Bearing Size	6208
UL	Recognized	CSA	Y
CE	Y	IP Code	55
Number of Speeds	1		

### Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	.25 Ohms	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	Single Special Extension	Assembly/Box Mounting	F2 ONLY
Outline Drawing	038165-1212	Connection Drawing	EE7308G

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/23/2023