



Nameplate Specifications

Output HP	20 Hp	Output KW	14.9 kW
Frequency	60 Hz	Voltage	575 V
Current	18.5 A	Speed	3520 rpm
Service Factor	1.25	Phase	3
Efficiency	91 %	Power Factor	88.6
Duty	Continuous	Insulation Class	F
Design Code	A	KVA Code	F
Frame	215TZ	Enclosure	Drip Proof Air Over
Thermal Protection	Thermostat	Ambient Temperature	40 °C
Drive End Bearing Size	6307	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	N	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Resistance Main	.485 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Assembly/Box Mounting	F1 ONLY
Connection Drawing	005102.13	Outline Drawing	038158-1240

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:03/30/2023