



Nameplate Specifications

Output HP	10 Hp	Output KW	7.5 kW
Frequency	60 Hz	Voltage	230 V
Current	39.0 A	Speed	1745 rpm
Service Factor	1.15	Phase	1
Efficiency	86.5 %	Power Factor	96.4
Duty	Continuous	Insulation Class	F
Design Code	L	KVA Code	G
Frame	215JM	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6309	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	Y	IP Code	12
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	JM	Overall Length	21.17 in
Frame Length	12.40 in	Shaft Diameter	1.125 in
Shaft Extension	4.5 in	Assembly/Box Mounting	F1 ONLY
Connection Drawing	005528.01	Outline Drawing	OL141431-1240