



Nameplate Specifications

Phase	3	Output HP	3 & 2 Hp
Output KW	2.2 & 1.5 kW	Voltage	230/460 & 190/380 V
Speed	1775 & 1480 rpm	Service Factor	1.0 & 1.0
Frame	213T	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	Thermostat	Efficiency	89.5 & 89.5 %
Ambient Temperature	71 °C	Frequency	60 & 50 Hz
Current	7.8/3.9 & 7.4/3.7 A	Power Factor	81
Duty	Continuous	Insulation Class	H
KVA Code	K	Drive End Bearing Size	6307
Opp Drive End Bearing Size	6208	UL	Recognized
CSA	Y	CE	Y
IP Code	56	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	4	Rotation	Reversible
Resistance Main	2.385 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T Both Sides	Assembly/Box Mounting	F2/F1 CAPABLE
Inverter Load	CONSTANT 1000:1		
Outline Drawing	038277-912	Connection Drawing	EE7308BT

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/23/2023