

PRODUCT INFORMATION PACKET

marathon®
Motors

Model No: 145TTFBD16031

Catalog No: GT3107A

Globetrotter® Close-Coupled Pump Motor, 2 HP, 3 Ph, 60 Hz, 208-230/460 V, 1800 RPM, 145JM Frame,
TEFC



Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord

Nameplate Specifications

| | | | |
|------------------------|----------------|----------------------------|-----------------------------|
| Output HP | 2 Hp | Output KW | 1.5 kW |
| Frequency | 60 Hz | Voltage | 208-230/460 V |
| Current | 5.8-5.4/2.7 A | Speed | 1745 rpm |
| Service Factor | 1.15 | Phase | 3 |
| Efficiency | 86.5 % | Power Factor | 80 |
| Duty | Continuous | Insulation Class | F |
| Design Code | B | KVA Code | L |
| Frame | 145JM | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| Drive End Bearing Size | 6206 | Opp Drive End Bearing Size | 6205 |
| UL | Listed | CSA | Y |
| CE | Y | IP Code | 43 |
| Hazardous Location | DIVISION 2 T2B | Number of Speeds | 1 |

Technical Specifications

| | | | |
|-----------------------|------------------------------|-------------------|----------------------------|
| Electrical Type | Squirrel Cage Inverter Rated | Starting Method | Line Or Inverter |
| Poles | 4 | Rotation | Reversible |
| Resistance Main | 9.55 Ohms | Mounting | Bolt-on Base |
| Motor Orientation | Horizontal | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | JM | Shaft Diameter | 0.875 in |
| Assembly/Box Mounting | F1/F2 CAPABLE | Inverter Load | CONSTANT 4:1/VARIABLE 10:1 |
| Connection Drawing | EE7308 | Outline Drawing | SS621064-850 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/13/2023



| | | | | | | | | | | | |
|---|--|----------------|---------|--------------------------------|-----------------|--|---------------------|-------------|------|----|------|
| | | | | TOLERANCES UNLESS SPECIFIED | |  Regal Beloit America, Inc. | DRAWN RM 11/20/1990 | | | | |
| 5 | CHG TO REGAL LOGO | SL 09/10/2015 | AB | DEC. | INCHES | | CHK ML 11/21/1990 | | | | |
| 4 | REVISED IEC NOTATIONS | MSG 11/15/2011 | CMN | .X | ±.1 | | APPD SAS 04/24/2003 | | | | |
| 3 | ADDED IEC NOTATIONS... (U1), (V1) ETC. MU95194 | MSG 5/10/2010 | MJS | .XX | ±.02 | | SCALE 1=1 | | | | |
| 2 | ADDED THE OPTIONAL CORD CONNECTION MU46318 | RDH 04/24/2003 | DRS | .XXX | ±.005 | | REF | | | | |
| 1 | REDRAWN | RM 11/20/1990 | | .XXXX | ±.0005 | MAT'L | FMF | | | | |
| NO. | REVISION | BY & DATE | CHK | ANG | ±7"30" | FINISH | PREV | | | | |
| THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT | | | RFP | | CAD FILE ee7308 | | SIZE | DRAWING NO. | PAGE | OF | REV. |
| | | | DIST WP | | | | A | EE7308 | | | |



P.O. BOX 8003
WAUSAU, WI 54401-8003
PH. 715-675-3311

DATA VOLTS: 460

CERTIFICATION DATA SHEET

CUSTOMER:**ORDER #:****CONN. DIAGRAM:****OUTLINE:****WINDING:****SPEED:**

A-EE7308

A-SS621064-850

HAT4009

NONE

1

CUSTOMER P.O. #:**REFERENCE MODEL #:****CAT #:****CUSTOMER PART #:****MOUNTING:**

145TTFBD16031

GT3107A

F1/F2 CAPABLE

TYPICAL MOTOR PERFORMANCE DATA

| HP | KW | SYNC RPM | FL RPM | FRAME | ENCLOSURE | TYPE | KVA CODE | DESIGN |
|----|-----|----------|--------|-------|-----------|------|----------|--------|
| 2 | 1.5 | 1800 | 1745 | 145JM | TEFC | TFR | M | B |

| PH | HZ | VOLTS | AMPS | START TYPE | DUTY | INSL | S.F. | AMB | ELEV. |
|----|----|-------------|-------------|------------------|------|------|------|-----|-------|
| 3 | 60 | 208-230/460 | 5.8-5.4/2.7 | LINE OR INVERTER | CONT | F | 1.15 | 40 | 3300 |

| | | | | | | | |
|----------|------|------------|------|------------|------|---------|-------------------|
| F.L. EFF | 86.5 | 3/4 LD EFF | 86.2 | 1/2 LD EFF | 84.2 | GTD EFF | ELECT. TYPE |
| F.L. PF | 80.0 | 3/4 LD PF | 72.0 | 1/2 LD PF | 58.0 | 84.0 | SQ CAGE INV RATED |

| F.L. TORQUE | | LR AMPS @ 460 V | | L.R. TORQUE | | B.D. TORQUE | | F.L. RISE (° C) | |
|-------------|-------|-----------------|--|-------------|------------|-------------|------------|-----------------|--|
| 6.0 | LB-FT | 24.0 | | 21.3 | LB-FT 355% | 25.0 | LB-FT 417% | 70 | |

| | | | | | | | | |
|------------------------|--------|-------|-------------------------|---------------------------|-----------------|-------------|---------|-----------|
| SOUND PRESSURE @ 3 FT. | SOUND | POWER | ROTOR WK ² | MAX. LOAD WK ² | SAFE STALL TIME | STARTS/HOUR | APPROX. | MOTOR WGT |
| 62 dBA | 71 dBA | | 0.12 LB-FT ² | 10 LB-FT ² | 10 SEC. | 2 | 48 | LB. |

*** SUPPLEMENTAL INFORMATION ***


| | | | | | | | | |
|-----------------|------------------|------------|-------------------|-------------|--------------------|------------|---------|---------------|
| DE BRACKET TYPE | ODE BRACKET TYPE | MOUNT TYPE | MOTOR ORIENTATION | SEVERE DUTY | HAZARDOUS LOCATION | DRIP COVER | SCREENS | PAINT |
| C-FACE | STANDARD | BOLT-ON | HORIZONTAL | NO | NONE | YES | NONE | BLUE (ENAMEL) |

| | | | | | | | |
|----------|--------|------------|------------|-------------|-------|-------------------------|----------------|
| BEARINGS | GREASE | SHAFT TYPE | SPECIAL DE | SPECIAL ODE | SHAFT | MATERIAL | FRAME MATERIAL |
| DE | ODE | | | | | | |
| BALL | BALL | POLYREX EM | JM | NONE | NONE | 1045 HOT ROLLED (C-204) | ROLLED STEEL |
| 6206 | 6205 | | | | | | |

| | | | | | | | |
|-------------|------------|-----------|-----------|-------------|---------|-------|---------|
| THERMOSTATS | PROTECTORS | WDG RTD's | BRG RTD's | THERMISTORS | CONTROL | SPACE | HEATERS |
| NONE | NOT | NONE | NONE | NONE | FALSE | | NA |

| | | | | | | |
|--------------|--------------|--------------|--------------|--------------|--------------------|-------|
| R1 (ohms/ph) | R2 (ohms/ph) | X1 (ohms/ph) | X2 (ohms/ph) | Xm (ohms/ph) | VIBRATION (in/sec) | FLOAT |
| 6.332 | 4.574 | 7.749 | 7.182 | 193.725 | 0.150 | ODE |

| | | |
|---------------------------------|---|-------------------------------|
| * N O T E s * | INVERTER TORQUE: CONSTANT 4:1/VARIABLE 10:1 | |
| | INV. HP SPEED RANGE: NONE | |
| | ENCODER: NONE | |
| | NONE | |
| | NONE PPR | |
| PREPARED BY: _____ | | BRAKE: NONE |
| DATE: 2/22/2022 | | NONE |
| | | FT-LB: NA |
| | | VOLTAGE: NONE |
| | | HZ: _____ |
| FORM: 3531 REV. 4 2/27/06 | | UL: V - LIME-INS.CONST UL REC |



EC Declaration of Conformity

The undersigned representing
the manufacturer:

Regal Beloit America
100 East Randolph St.
Wausau, WI 54401

and the authorized representative
established within the Community:

Marathon Electric UK
6F Thistleton Road Ind. Estate
Market Overton
Oakham, Rutland LE15 7PP UK

are committed to providing customers with products that comply with applicable regulations and international protocols to which they are subject, including the requirements of the European Parliament Directive on the Harmonization of the laws relating to electrical equipment designed for use within certain voltage limits (2014/35/EU).

Regal Beloit America declares that the following product(s), to which this declaration relates, are in conformity with the relevant sections of the EC standards listed below.

This statement supersedes any statements previously issued pertaining to the product(s) listed below and is subject to change without notice.

Model No : 145TTFBD16031

(Model No. may contain prefix and/or suffix characters)

Catalog No : GT3107A

Rework No : N/A

Directives :


Low Voltage Directive 2014/35/EU

Harmonized Standards Used :

EN 60034-1: 2010 (IEC 60034-1: 2010)

EN 60034-5: 2001/A1:2007 (IEC 60034-5: 2000/A1:2006)

Authorized Representative:



Michael A. Logsdon
Vice President, Technology

Authorized Representative in the Community:



Julian Clark
Marketing Engineer

Created on 09/01/2022

CE 22