

PRODUCT INFORMATION PACKET



Model No: E3009
Catalog No: E3009
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	7.5 Hp
Output KW	5.6 kW	Voltage	230/460 V
Speed	1750 r/min	Service Factor	1.15
Frame	213TC	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Frequency	60 Hz	Current	19.0/9.5 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y
Number of Speeds	1		

Technical Specifications

Rotation	Reversible	Mounting	Rigid Base
Drive End Bearing	Ball	Opp Drive End Bearing	Ball

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025