



## Nameplate Specifications

Output HP	30 Hp	Output KW	22.4 kW
Frequency	60 Hz	Voltage	208-230/460 V
Current	76.0-70.0/35.0 A	Speed	1760 rpm
Service Factor	1.15	Phase	3
Efficiency	91.5 %	Power Factor	87.7
Duty	Continuous	Insulation Class	F
Design Code	C	KVA Code	G
Frame	286TC	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No	Ambient Temperature	40 °C
Drive End Bearing Size	6311	Opp Drive End Bearing Size	6309
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

## Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	0 Ohms	Mounting	Round
Motor Orientation	Nan	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	NAN
Connection Drawing	004172.01	Outline Drawing	16957960

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/26/2021