

Nameplate Specifications

| | | | |
|------------------------|---------------|----------------------------|-----------------------------|
| Phase | 3 | Output HP | 15 Hp |
| Output KW | 11.2 kW | Voltage | 230/460 V |
| Speed | 1770 rpm | Service Factor | 1.15 |
| Frame | 160M | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Efficiency | 91 % |
| Ambient Temperature | 40 °C | Frequency | 60 Hz |
| Current | 36.5/18.3 A | Power Factor | 83 |
| Duty | Continuous | Insulation Class | F |
| Design Code | B | KVA Code | K |
| Drive End Bearing Size | 6309 | Opp Drive End Bearing Size | 6309 |
| UL | No | CSA | N |
| CE | Y | IP Code | 55 |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|------------------------------|-----------------------|--|
| Electrical Type | Squirrel Cage Inverter Rated | Starting Method | Part Wdg Start & Wye Start Delta Run Or Inverter |
| Poles | 4 | Rotation | Reversible |
| Resistance Main | .555 Ohms | Mounting | Rigid Base |
| Motor Orientation | Horizontal | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Cast Iron |
| Shaft Type | IEC | Assembly/Box Mounting | F1/F2 CAPABLE |
| Outline Drawing | B-SS620364 | Connection Drawing | A-EE7308AA |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/07/2024