

PRODUCT INFORMATION PACKET



Model No: 170001.00

Catalog No: 170001.00

General Purpose Motor, 20 & 15 HP, 3 Ph, 60 & 50 Hz, 208-230/460 & 190/380 V, 1200 & 1000 RPM,
286T Frame, TEFC



Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E







Nameplate Specifications

| | | | |
|------------------------|------------------------|----------------------------|-----------------------------|
| Phase | 3 | Output HP | 20 & 15 Hp |
| Output KW | 14.9 & 11.2 kW | Voltage | 208-230/460 & 190/380 V |
| Speed | 1185 & 980 rpm | Service Factor | 1.15 & 1.15 |
| Frame | 286T | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Efficiency | 92.4 & 91.7 % |
| Ambient Temperature | 40 °C | Frequency | 60 & 50 Hz |
| Current | 55-53.5/26.8 & 48/24 A | Power Factor | 75 |
| Duty | Continuous | Insulation Class | F |
| Design Code | B | KVA Code | G |
| Drive End Bearing Size | 6311 | Opp Drive End Bearing Size | 6309 |
| UL | Recognized | CSA | Y |
| CE | Y | IP Code | 43 |
| Number of Speeds | 1 | | |


Technical Specifications

| | | | |
|-------------------|-----------------------------|-----------------------|---------------------|
| Electrical Type | Squirrel Cage Induction Run | Starting Method | Wye Start Delta Run |
| Poles | 6 | Rotation | Reversible |
| Mounting | Rigid Base | Motor Orientation | Horizontal |
| Drive End Bearing | Ball | Opp Drive End Bearing | Ball |
| Frame Material | Cast Iron | Shaft Type | T |
| Overall Length | 27.83 in | Shaft Diameter | 1.875 in |
| Shaft Extension | 4.62 in | Assembly/Box Mounting | F1/F2 CAPABLE |
| Outline Drawing | 16953960 | Connection Drawing | 004172.03 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/22/2023



| FRAME DESIGN | "C" | "BV" | "BS" |
|--------------|-------|-------|------|
| 284T | 26.26 | 9.65 | |
| 286T | 27.83 | 10.43 | 5.51 |


| | | | | | | | | | | | |
|--|----------------------------------|--------------|------|--------------------------------|--------|--|--------------------------------------|-------------|------|----|------|
| | | | | TOLERANCES UNLESS SPECIFIED | |  REGAL-BELOIT CORPORATION | DRAWN CJK 07/16/01 | | | | |
| | | | | DEC. | INCHES | | CHK | | | | |
| | | | | .X | ±.1 | | APPD | | | | |
| 03 | ECO-0048910, REVISED 'BA' DIM. | RFH 04/04/14 | EH | .XX | ±.03 | | TITLE OUTLINE-280T FRAME, TEFC-RIGID | | | | |
| 02 | REDRAWN TO CURRENT CAD STANDARDS | CJK 07/13/99 | | .XXX | ±.005 | NEW CONDUIT BOX | | | | | |
| 01 | ADDED HOLE FOR 286T BASE | JKK 11/01/01 | | .XXXX | ±.0005 | MAT'L. CAST IRON | | | | | |
| NO. | REVISION | BY & DATE | CHK | ANG | ±1/2" | FINISH | | | | | |
| THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT | | | RFP | CAD FILE | | | SIZE | DRAWING NO. | PAGE | OF | REV. |
| | | | DIST | | | | A | 169539-60 | | | 03 |

WYE - DELTA STARTING USEABLE ON 2,4 AND 6 POLE MOTORS.

LOW VOLTAGE CONNECTION



HIGH VOLTAGE CONNECTION



REFER TO THE WYE-DELTA STARTER CONNECTION INSTRUCTIONS FOR PROPER CONNECTION OF POWER LINES TO STARTER.


PART WINDING START USABLE ON 4 & 6 POLE MOTORS LOW VOLTAGE CONNECTION ONLY



REFER TO THE PART WINDING STARTER INSTRUCTIONS FOR PROPER CONNECTION OF POWER LINES TO STARTER.

REFER TO THE CUTLER - HAMMER OR EQUIV. FOR PROPER SELECTION OF OVERLOAD HEATER COILS.

LINE LEADS



12 LEAD DELTA CONNECTION ACROSS THE LINE START (FOR Y START DELTA RUN, REMOVE THE JUMPERS)

LOW VOLTAGE
(MUST BE REWIRED AS SHOWN)

HIGH VOLTAGE
(FACTORY WIRED FOR HIGH VOLTAGE AS SHOWN)



| | | | | TOLERANCES UNLESS SPECIFIED | | <div>LEESON</div> <div>ELECTRIC MOTORS GEARMOTORS AND DRIVES</div> | DRAWN C/W 08/28/02 | |
|---|----------|-----------|-----|--------------------------------|---------|--|--------------------|-------------|
| | | | | DEC. | INCHES | | CHK | |
| | | | | X | ± .1 | | APPO | |
| | | | | XX | ± .01 | | SCALE | 1:1 |
| | | | | XXX | ± .005 | | REF | |
| | | | | XXXX | ± .0005 | MAT'L | FMF | |
| NO. | REVISION | BY & DATE | CHK | ANG | ± 1/2° | FINISH | PREV | |
| THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK. ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED. THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT. | | | | REP | | CAD FILE | 00417203 | SIZE |
| | | | | DST | | | | A |
| | | | | | | | | DRAWING NO. |
| | | | | | | | | 004172-03 |
| | | | | | | | | REV. |

ERROR: syntaxerror
OFFENDING COMMAND: --nostringval--

STACK:

/CB
-dictionary-
/Pscript_WinNT_Compat
-dictionary-