

PRODUCT INFORMATION PACKET



Model No: 513999G-AV
Catalog No: 513999G-AV
B-513999G-AV COV PL MCH/SCREEN



Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Technical Specifications



This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/04/2025



SECTION A-A

DRAWING REVISION D	REVISION BY JP	DATE 04-18-2019
ECO ECO-0165346	APPROVED BY DJK	DATE 04-22-2019
ECO DESCRIPTION CORRECTED MODEL		
COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.		

TOLERANCES UNLESS OTHERWISE SPECIFIED:			
DEC.	INCH	mm	ANGLE
.X	\pm 0.1	[\pm 2.5]	\pm 7° 30"
.XX	\pm 0.02	[\pm 0.51]	
.XXX	\pm 0.005	[\pm 0.127]	
.XXXX	\pm 0.0005	[\pm 0.0127]	
REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.076/.381] X 45° CORNER FILLETS: R.02 [.51] MACHINED SURFACES: 200 INCH $\sqrt{\text{mm}}$ 5.1			
mm SHOWN IN [BRACKETS]			

DRAWN BY JJB	 Regal Beloit America, Inc.		
DATE 01-11-2011			
APPROVED BY MJS	DESCRIPTION FRACKET-MACHINING		
DATE 01-11-2011	440 FR - C'FACE - 16.50 AK - SCREEN		
REFERENCE D-513999	MATERIAL CSTG 513999	PROCESS/FINISH	
THIRD ANGLE PROJECTION 	SIZE B	DRAWING NUMBER 513999G	SHEET 1 OF 1