



Nameplate Specifications

Phase	3	Output HP	200 Hp
Output KW	149.0 kW	Voltage	575 V
Speed	3580 rpm	Service Factor	1.15
Frame	447TS	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	95.4 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	174.0 A	Power Factor	90.5
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Drive End Bearing Size	6314	Opp Drive End Bearing Size	6314
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Wye Start Delta Run
Poles	2	Rotation	Reversible
Mounting	Rigid Base	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Cast Iron	Shaft Type	TS
Overall Length	44.33 in	Shaft Diameter	2.375 in
Shaft Extension	4.76 in	Assembly/Box Mounting	F1/F2 CAPABLE
Connection Drawing	005190.01	Outline Drawing	B-SS622204LE