

Product Information Packet: Model No: 171813.60, Catalog No:171813.60
 171813.60..15/10HP..3550/2960RPM.254TC.TEFC.190/230/380/460V.3PH.60/50HZ.CONT.40C.1.25SF.RIGID C.....DRILL/ TAP SHFT END 3/4"-10
 RH.....

Nameplate Specifications

Output HP	15 Hp	Output KW	11.2 kW
Frequency	60 Hz	Voltage	208-230/460 V
Current	38.0-34.5/17.3 A	Speed	3550 rpm
Service Factor	1.25	Phase	3
Efficiency	92.4 %	Power Factor	88.5
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Frame	254TC	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	Thermostat	Ambient Temperature	40 °C
Drive End Bearing Size	6309	Opp Drive End Bearing Size	6308
UL	Recognized	CSA	N
CE	N	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Wye Start Delta Run Or Inverter
Poles	2	Rotation	Reversible
Resistance Main	.107 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Inverter Load	CONSTANT 10:1		
Outline Drawing	SS620679	Connection Drawing	4172.01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/01/2022