

PRODUCT INFORMATION PACKET



Model No: MGP0107-01C
Catalog No: MGP0107-01C
TERMINAL BOX ASSY - 18X18X10, W/KO

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E






Nameplate Specifications



Technical Specifications

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/04/2025



ASSEMBLY NOTES:

- MATERIAL/FINISH-SEE INDIVIDUAL PART DETAIL DRAWINGS.
- TOLERANCE EXCEPT WHERE NOTED: $\pm .50$ [$\pm .020$], ANGULAR: $\pm 0^\circ 30'$.
- MOUNT GASKET TO COVER & PUNCHED OUT $\phi 9.53$ [$\phi .375$] HOLES AROUND MOUNTING HOLES, 4 PL.

DRAWING REVISION L	REVISION BY NK	REV DATE/© DATE 03-29-2019	TOLERANCES (EXCEPT AS NOTED): DEC. mm INCH ANGLE NONE ± 3 [± 0.1] $\pm 0.5^\circ$.X ± 0.3 [± 0.01] .XX ± 0.13 [± 0.005] .XXX ± 0.013 [± 0.0005] REMOVE BURRS & BREAK SHARP EDGES: .08/.38 [.003/.015] X 45° CORNER FILLETS: R.5 [.02] MACHINED SURFACES: 125 $\sqrt{\text{mm}}$ 3.2 $\sqrt{\text{INCH}}$ INCH DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY				DRAWN BY TJP	 Regal Beloit America, Inc.			
ECO ECO-0164283	APPROVED BY MILES R HOYT	DATE 03-29-2019					DATE 02-23-17				
ECO DESCRIPTION REDRAWN IN SOLIDWORKS COPYRIGHT (PER REVISION DATE) REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.			DESCRIPTION TERMINAL BOX ASSY 18.13 X 18.13				APPROVED BY GLM				
							DATE 02-23-17				
							REFERENCE	MATERIAL		PROCESS/FINISH	
							THIRD ANGLE PROJECTION 	SIZE B	DRAWING NUMBER MGP0107		SHEET 1 OF 2

4

3

2

1



4 X 1/4-20 UNC-2A HEX WASHER HEAD
MACHINE SCREW X 19.05[0.75] LG

GASKET

4 X 1/4-20 UNC-2B J-STYLE CAGE NUT
OR ENGINEER APPROVED EQUIV.

TERMINAL BOX - BASE
PN: MMC0907-XX

TERMINAL BOX-COVER
PN:MMC0140-XX

DRAWING REVISION L	REVISION BY NK	REV DATE/© DATE 03-29-2019	TOLERANCES (EXCEPT AS NOTED): DEC. mm INCH ANGLE NONE ±3 [±0.1] ±0.5° .X ±0.3 [±0.01] .XX ±0.13 [±0.005] .XXX ±0.013 [±0.0005] REMOVE BURRS & BREAK SHARP EDGES: .08/.38 [.003/.015] X 45 ° CORNER FILLETS: R.5 [.02] MACHINED SURFACES: 125/ 3.2 INCH mm INCH DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY	DRAWN BY TJP	 Regal Beloit America, Inc.		
ECO ECO-0164283	APPROVED BY MILES R HOYT	DATE 03-29-2019		DATE 02-23-17	DESCRIPTION TERMINAL BOX ASSY 18.13 X 18.13		
ECO DESCRIPTION REDRAWN IN SOLIDWORKS				APPROVED BY GLM			
COPYRIGHT (PER REVISION DATE) REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.				DATE 02-23-17	MATERIAL		PROCESS/FINISH
				REFERENCE			
				THIRD ANGLE PROJECTION		SIZE B	DRAWING NUMBER MGP0107