

PRODUCT INFORMATION PACKET



Model No: E608R
Catalog No: E608R
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E




**Nameplate Specifications**

Phase	3	Output HP	40.0 Hp
Output KW	29.8 kW	Voltage	200 V
Speed	1760 r/min	Service Factor	1.15
Frame	D324T	Enclosure	Drip Proof
Efficiency	93 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	113.0 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Reversible Counterclockwise
Drive End Bearing	312sf	Opp Drive End Bearing	210sf
Frame Length	15.50 in		
Connection Drawing	80022803.PCX		


This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025



80022803

NOTES:

1. DRAWING FOR REPRESENTATION ONLY. ACTUAL CONNECTION DIAGRAM IS COMPUTER GENERATED AND PRINTED ON ADHESIVE NAMEPLATE 800163.
2. RESERVED FOR THREE PHASE CONNECTIONS.

				TOLERANCES UNLESS SPECIFIED		REGAL-BELOIT 	DRAWN JVD 03-30-2021	
				DEC.	INCHES		CHK	AJAY 03-30-2021
				.X	±.1	TITLE CONNECTION DIAGRAM		APPD AJAY 03-30-2021
				.XX	±.02			SCALE 1=1
				.XXX	±.005			REF 800228
C	UPDATED REGAL LOGO IN TITLE BLOCK	JVD 03-30-2021	AJAY .XXXX	±.0005	MAT'L.		FMF	
NO.	REVISION	BY & DATE	CHK	ANG	±7'30"	FINISH	PREV	
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT						RFP 03-30-2021	CAD FILE 80022803-S01	SIZE A
						DIST LB-PR		DRAWING NO. 80022803-S01
								PAGE OF
								REV. C