

Nameplate Specifications

Phase	1	Output HP	2 Hp
Output KW	1.5 kW	Voltage	230 V
Speed	1750 rpm	Service Factor	1.15
Frame	182JMV	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	75.5 %
Ambient Temperature	50 °C	Frequency	60 Hz
Current	11.5 A	Power Factor	74
Duty	Continuous	Insulation Class	F
Design Code	L	KVA Code	J
Drive End Bearing Size	6207	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Resistance Main	1.17 Ohms	Mounting	Round
Motor Orientation	Shaft Down	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	JM	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	035786-900	Connection Drawing	005033.01ME

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2023