

### Nameplate Specifications

Phase	<b>3</b>	Output HP	<b>1.50 Hp</b>
Output KW	<b>1.1 kW</b>	Voltage	<b>575 V</b>
Speed	<b>1180 rpm</b>	Service Factor	<b>1.15</b>
Frame	<b>182JPV</b>	Enclosure	<b>Drip Proof</b>
Thermal Protection	<b>No Protection</b>	Efficiency	<b>86.5 %</b>
Ambient Temperature	<b>40 °C</b>	Frequency	<b>60 Hz</b>
Current	<b>1.8 A</b>	Power Factor	<b>69</b>
Duty	<b>Continuous</b>	Insulation Class	<b>F</b>
Design Code	<b>B</b>	KVA Code	<b>J</b>
Drive End Bearing Size	<b>6206</b>	Opp Drive End Bearing Size	<b>6203</b>
UL	<b>Recognized</b>	CSA	<b>Y</b>
CE	<b>Y</b>	IP Code	<b>22</b>
Number of Speeds	<b>1</b>		

### Technical Specifications

Electrical Type	<b>Squirrel Cage Inverter Rated</b>	Starting Method	<b>Line Or Inverter</b>
Poles	<b>6</b>	Rotation	<b>Reversible</b>
Resistance Main	<b>8.05 Ohms</b>	Mounting	<b>Rigid Base</b>
Motor Orientation	<b>Horizontal Or Shaft Down</b>	Drive End Bearing	<b>Ball</b>
Opp Drive End Bearing	<b>Ball</b>	Frame Material	<b>Rolled Steel</b>
Shaft Type	<b>JP</b>	Overall Length	<b>19.44 in</b>
Shaft Diameter	<b>0.875 in</b>	Shaft Extension	<b>7.35 in</b>
Assembly/Box Mounting	<b>F1 ONLY</b>		
Connection Drawing	<b>EE7300</b>	Outline Drawing	<b>SS620570-182T</b>