

Nameplate Specifications

Phase	3	Output HP	2 & 0.50 Hp
Output KW	1.5 & 0.37 kW	Voltage	460 & 460 V
Speed	1775 & 885 rpm	Service Factor	1.15 & 1.15
Frame	182T	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	83 & 65 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	2.5 & 1.5 A	Power Factor	79.5
Duty	Continuous	Insulation Class	F
Design Code	2VT	KVA Code	L
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6203
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	2		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4//8	Rotation	Reversible
Resistance Main	11.1364 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Shaft Diameter	1.125 in
Assembly/Box Mounting	F1/F2 CAPABLE		
Connection Drawing	EE7317	Outline Drawing	SS600198-100