

Nameplate Specifications

Output HP	3,0.75 Hp	Output KW	2.2 kW
Frequency	60 Hz	Voltage	200-230 V
Current	8.8-8,3.8-3.6 A	Speed	1725,869 rpm
Service Factor	1.15	Phase	3
Efficiency	81.3 %	Power Factor	88.3
Duty	Continuous	Insulation Class	F
Design Code	1VT	KVA Code	J
Frame	182T	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	2		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4/8	Rotation	Reversible
Resistance Main	6.4 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1 ONLY
Connection Drawing	005200-01ME	Outline Drawing	035457-1000

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/07/2022