

Nameplate Specifications

Phase	3	Output HP	2 & 0.50 Hp
Output KW	1.5 & 0.37 kW	Voltage	460 & 460 V
Speed	1755 & 870 rpm	Service Factor	1.15 & 1.15
Frame	182T	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	80 & 64 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	3 & 1.2 A	Power Factor	81
Duty	Continuous	Insulation Class	B
Design Code	2VT	KVA Code	J
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6203
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	2		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4//8	Rotation	Reversible
Resistance Main	14.8 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Overall Length	13.22 in
Frame Length	6.25 in	Shaft Diameter	1.125 in
Shaft Extension	2.75 in	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	A-SS65625-625	Connection Drawing	A-EE7317