

### Nameplate Specifications

Phase	3	Output HP	2 & 0.89 Hp
Output KW	1.5 & 0.66 kW	Voltage	200-230 & 200-230 V
Speed	1760 & 1155 rpm	Service Factor	1.15 & 1.15
Frame	182T	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	81 & 75.5 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	6.5-6.3 & 3.5-3.5 A	Power Factor	73.5
Duty	Continuous	Insulation Class	B
Design Code	2VT	KVA Code	L
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6203
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	2		

### Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4//6	Rotation	Reversible
Resistance Main	10.34 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Overall Length	13.72 in
Frame Length	6.75 in	Shaft Diameter	1.125 in
Shaft Extension	2.75 in	Assembly/Box Mounting	F1/F2 CAPABLE
Connection Drawing	A-EE7317	Outline Drawing	A-SS65625-675