

Nameplate Specifications

Phase	1	Output HP	7.50 & 10 Hp
Output KW	5.6 & 7.5 kW	Voltage	230 & 230 V
Speed	3525 & 3485 rpm	Service Factor	1.35 & 1.0
Frame	184TZ	Enclosure	Drip Proof Air Over
Thermal Protection	No Protection	Efficiency	84 & 80 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	30 & 42 A	Power Factor	96.5
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	E
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	N	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	2	Rotation	Selective Counterclockwise
Resistance Main	.222 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Overall Length	16.43 in
Frame Length	8.75 in	Shaft Diameter	1.125 in
Shaft Extension	3.5 in	Assembly/Box Mounting	F3
Connection Drawing	A-EE9048PG	Outline Drawing	A-SS68830-875