

Nameplate Specifications

Output HP	8 Hp	Output KW	6.0 kW
Frequency	60 Hz	Voltage	208-230 V
Current	35.0-32.0 A	Speed	3450 rpm
Service Factor	1.15	Phase	1
Efficiency	84 %	Power Factor	96
Duty	Continuous	Insulation Class	F
Design Code	L	KVA Code	H
Frame	184T	Enclosure	Drip Proof
Thermal Protection	Manual	Ambient Temperature	40 °C
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	2	Rotation	Fixed Clockwise
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1 ONLY
Connection Drawing	005056.61ME	Outline Drawing	035562-1250

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/07/2022