



### Nameplate Specifications

Phase	1	Output HP	6 Hp
Output KW	4.5 kW	Voltage	200-208 V
Speed	1760 rpm	Service Factor	1
Frame	184TC	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	Manual	Efficiency	84 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	28.0-27.1 A	Power Factor	94.1
Duty	Continuous	Insulation Class	F
Design Code	L	KVA Code	H
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized ( Not Protector)	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

### Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Fixed Clockwise
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F3
Outline Drawing	035615-1200	Connection Drawing	005450.04ME

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2023