

Nameplate Specifications

Phase	1	Output HP	3 Hp
Output KW	2.2 kW	Voltage	115/208-230 V
Speed	1755 rpm	Service Factor	1
Frame	184T	Enclosure	Totally Enclosed Air Over
Thermal Protection	No Protection	Efficiency	80 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	28.0/14.6-14.0 A	Power Factor	88
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	K
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Resistance Main	.68 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1 ONLY
Outline Drawing	035737-950	Connection Drawing	00505401ME

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2023