

### Nameplate Specifications

|                        |                 |                            |             |
|------------------------|-----------------|----------------------------|-------------|
| Phase                  | 3               | Output HP                  | 3 & 1.33 Hp |
| Output KW              | 2.2 & 0.99 kW   | Voltage                    | 460 & 460 V |
| Speed                  | 1775 & 1180 rpm | Service Factor             | 1.15 & 1.15 |
| Frame                  | 184T            | Enclosure                  | Drip Proof  |
| Thermal Protection     | No Protection   | Efficiency                 | 82 & 76 %   |
| Ambient Temperature    | 40 °C           | Frequency                  | 60 & 60 Hz  |
| Current                | 4.5 & 2.5 A     | Power Factor               | 72.5        |
| Duty                   | Continuous      | Insulation Class           | F           |
| Design Code            | 2VT             | KVA Code                   | M           |
| Drive End Bearing Size | 6206            | Opp Drive End Bearing Size | 6203        |
| UL                     | Recognized      | CSA                        | Y           |
| CE                     | Y               | IP Code                    | 22          |
| Number of Speeds       | 2               |                            |             |

### Technical Specifications

|                       |                             |                   |                 |
|-----------------------|-----------------------------|-------------------|-----------------|
| Electrical Type       | Squirrel Cage Induction Run | Starting Method   | Across The Line |
| Poles                 | 4//6                        | Rotation          | Reversible      |
| Resistance Main       | 15.0678 Ohms                | Mounting          | Rigid Base      |
| Motor Orientation     | Horizontal                  | Drive End Bearing | Ball            |
| Opp Drive End Bearing | Ball                        | Frame Material    | Rolled Steel    |
| Shaft Type            | T                           | Shaft Diameter    | 1.125 in        |
| Assembly/Box Mounting | F1/F2 CAPABLE               |                   |                 |
| Connection Drawing    | EE7317                      | Outline Drawing   | SS600198-200    |