

Nameplate Specifications

Phase	3	Output HP	3 & 1.33 Hp
Output KW	2.2 & 0.99 kW	Voltage	200-230 & 200-230 V
Speed	1775 & 1180 rpm	Service Factor	1.15 & 1.15
Frame	184T	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	82 & 76 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	9-8.5 & 5-4.98 A	Power Factor	72.5
Duty	Continuous	Insulation Class	F
Design Code	2VT	KVA Code	M
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6203
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	2		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4//6	Rotation	Reversible
Resistance Main	15.0678 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Shaft Diameter	1.125 in
Assembly/Box Mounting	F1/F2 CAPABLE		
Outline Drawing	SS600198-200	Connection Drawing	EE7317