

Nameplate Specifications

Phase	3	Output HP	5 Hp
Output KW	3.7 kW	Voltage	230/460 V
Speed	1765 rpm	Service Factor	1.15
Frame	184T	Enclosure	Drip Proof
Thermal Protection	Automatic	Efficiency	89.5 %
Ambient Temperature	50 °C	Frequency	60 Hz
Current	13.0/6.5 A	Power Factor	80
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	K
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	Y	IP Code	12
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	2.56 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1 ONLY
Outline Drawing	035731-1000	Connection Drawing	005010.43ME

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2023