

Nameplate Specifications

Phase	3	Output HP	5 Hp
Output KW	3.7 kW	Voltage	200-208 V
Speed	1756 rpm	Service Factor	1.15
Frame	184T	Enclosure	Drip Proof
Thermal Protection	Automatic	Efficiency	87.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	15.0-14.7 A	Power Factor	80.4
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	j
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Overall Length	13.19 in
Frame Length	9.00 in	Shaft Diameter	1.125 in
Shaft Extension	2.81 in	Assembly/Box Mounting	F1/F2 Capable
Connection Drawing	005019.01ME	Outline Drawing	035658-900