



Nameplate Specifications

Phase	3	Output HP	2,0.89 Hp
Output KW	1.5 kW	Voltage	415 V
Speed	1460,970 rpm	Service Factor	1.15
Frame	184T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	75 %
Ambient Temperature	50 °C	Frequency	50 Hz
Current	3.5,2 A	Power Factor	80
Duty	Continuous	Insulation Class	F
Design Code	2VT	KVA Code	M
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	2		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4//6	Rotation	Reversible
Resistance Main	5.345 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	035536-850	Connection Drawing	005046.01ME

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/20/2023