



Nameplate Specifications

Phase	3	Output HP	0.75 & 0.75 Hp
Output KW	0.56 & 0.56 kW	Voltage	230/460 & 200/400 V
Speed	3455 & 2795 rpm	Service Factor	1.15 & 1.0
Frame	D71	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	78 & 74 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	2.4/1.2 & 2.8/1.4 A	Power Factor	74
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	J
Drive End Bearing Size	6202	Opp Drive End Bearing Size	6202
UL	Recognized	CSA	Y
CE	Y	IP Code	55
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	2	Rotation	Reversible
Resistance Main	7.7 Ohms	Mounting	B3
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Aluminum
Shaft Type	IEC	Assembly/Box Mounting	F3
Inverter Load	CONSTANT 10:1		
Outline Drawing	OL19204030	Connection Drawing	00546505