

PRODUCT INFORMATION PACKET



Model No: 192011.30

Catalog No: 192011.30

Obsolete Replaced by 192011.00..1/4HP-0.18kW..1800RPM.D63.TEFC.230/460V.3PH.60HZ.CONT.40C..B3.....

.....

Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications




Phase	3	Output HP	0.25 & 0.25 Hp
Output KW	0.19 & 0.19 kW	Voltage	230/460 & 200/400 V
Speed	1655 & 1325 rpm	Service Factor	1.15 & 1.15
Frame	D63	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	68 & 64 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	1.2/0.6 & 1.2/0.6 A	Power Factor	60
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	H
Drive End Bearing Size	6201	Opp Drive End Bearing Size	6201
UL	Recognized	CSA	Y
CE	Y	IP Code	55
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	4	Rotation	Reversible
Resistance Main	97.12 Ohms	Mounting	B3
Motor Orientation	Horizontal Or Up Or Down	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Aluminum
Shaft Type	IEC	Assembly/Box Mounting	F3
Inverter Load	CONSTANT 20:1		
Outline Drawing	OL19201130	Connection Drawing	00546505

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/22/2023


CAT. NO.
192010.30
192020.30
192011.30
192088.30
192097.30
192089.30



Bases are removable and able to mount in all locations - 6:00, 9:00, 3:00.

TOLERANCES UNLESS SPECIFIED				REGAL REGAL-BELOIT CORPORATION		DRAWN	
DEC. INCHES						CHK	
X ±.1						APPD	
XX ±.03				TITLE		SCALE	
XXX ±.005						REF	
XXXX ±.0005				MAT'L		FIN	
NO. REVISION				FINISH		PREV	
BY & DATE				CAD FILE		SIZE	
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP		DRAWING NO.	
				DIST		B	
						REV.	



				TOLERANCES UNLESS SPECIFIED	 REGAL-BELOIT CORPORATION	DRAWN
			DEC.	INCHES		CHK
			.X	±.1		APP'D
			.XX	±.03		SCALE
			.XXX	±.005		REF
			.XXXX	±.0005		FNF
NOL	REVISION	BY & DATE	CHK	ANG	FINISH	PREV
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - NO NET SCALE THIS PRINT						RFP
						CAD FILE
						SIZE B
						DRAWING NO.
						REV.