



Nameplate Specifications

Phase	3	Output HP	0.25 & 0.25 Hp
Output KW	0.19 & 0.19 kW	Voltage	230/460 & 200/400 V
Speed	1105 & 885 rpm	Service Factor	1.15 & 1.0
Frame	D71C	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	66 & 62 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	1.2/0.6 & 1.2/0.6 A	Power Factor	62
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	G
Drive End Bearing Size	6202	Opp Drive End Bearing Size	6202
UL	Recognized	CSA	Y
CE	Y	IP Code	55
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	6	Rotation	Reversible
Resistance Main	0 Ohms	Mounting	B3
Motor Orientation	Horizontal Or Up Or Down	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Aluminum
Shaft Type	IEC	Assembly/Box Mounting	F3
Inverter Load	CONSTANT 20:1		
Outline Drawing	OL19201930	Connection Drawing	00546505