



Nameplate Specifications

Phase	3	Output HP	5.50 & 4 Hp
Output KW	4.1 & 3.0 kW	Voltage	230/460 & 200/400 V
Speed	3510 & 2930 rpm	Service Factor	1.15 & 1.15
Frame	112M	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	89.5 & 90.2 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	12.6/6.3 & 10.8/5.4 A	Power Factor	91
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	J
Drive End Bearing Size	6306	Opp Drive End Bearing Size	6306
UL	Recognized	CSA	Y
CE	Y	IP Code	55
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	2	Rotation	Reversible
Mounting	Rigid Base	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Cast Iron	Shaft Type	IEC
Overall Length	16.14 in	Shaft Diameter	1.125 in
Shaft Extension	2.36 in	Assembly/Box Mounting	F3
Connection Drawing	5465.01	Outline Drawing	SS622369