

PRODUCT INFORMATION PACKET



Model No: 199029.00

Catalog No: 199029.00

Obsolete Replaced by B199029.00..40HP..1200RPM.364T.TEFC.230/460V.3PH.60HZ.CONT.40C.1.15SF.RIGID...
...GENERAL PURPOSE.....



Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E






Nameplate Specifications

Phase	3	Output HP	40 & 30 Hp
Output KW	30.0 & 22.4 kW	Voltage	230/460 & 190/380 V
Speed	1188 & 990 rpm	Service Factor	1.15 & 1.15
Frame	364T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	94.1 & 94.1 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	94/47 & 87/43.5 A	Power Factor	83
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Drive End Bearing Size	6314	Opp Drive End Bearing Size	6313
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	6	Rotation	Reversible
Resistance Main	.1559 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Inverter Load	CONSTANT 20:1		
Outline Drawing	SS620115	Connection Drawing	EE7308AA-LE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/22/2023




<DIMENSIONS IN TABLE ARE CONSIDERED REFFERENCE>

364T	36.61	18.50	11.25	7.99
365T	38.39	20.28	12.25	8.88
FRAME	C	B	2F	BS

<MAY NOT BE DRAWN TO SCALE>

				TOLERANCES UNLESS SPECIFIED		 REGAL-BELOIT CORPORATION	DRA		
				DEC.	INCHES		CHK		
				.X	±.1		APP		
				.XX	±.03	TITLE OUTLINE 364/365T FR. - TEFC - CAST IRON	SCA		
K	CORRECTED DESCRIPTION ECO-0112150	WGJ 10/31/16	EH	XXX	±.005		REF		
1	ADDED 'BS' DIM. PER. ECO-0048910	RFH04/07/2014	EH	XXXX	±.0005	MAT'L.	FMF		
NO.	REVISION	BY & DATE	CHK	ANG	±1/2	FINISH	PRE		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP		CAD FILE	SS620115	SIZE	DRAWING NO.
				DIST				B	SS62





CERTIFICATION DATA SHEET

**1051 CHEYENNE AVE.
GRAFTON, WI 53024
PH. 262-377-8810**

CONN. DIAGRAM: EE7308AA-LE

CATALOG #: 199029.00

OUTLINE: SS620115

MOUNTING: F1/F2 CAPABLE

WINDING #: CHT36460001 1

TYPICAL MOTOR PERFORMANCE DATA

HP	kW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
40&30	30.0&22.4	1200	1188&990	364T	TEFC	G	B

PH	Hz	VOLTS	AMPS	START TYPE	DUTY	INSL	S.F.	AMB°C
3	60/50	230/460&190/380	94/47&87/43.5	LINE OR INVERTER	CONTINUOUS	F1	1.15/1.15	40

FULL LOAD EFF:	94.1&94.1	3/4 LOAD EFF:	94.5	1/2 LOAD EFF:	94.1	GTD. EFF		ELEC. TYPE
FULL LOAD PF:	83&83	3/4 LOAD PF:	78	1/2 LOAD PF:	69	94.1		SQ CAGE INV RATED

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
177 LB-FT	556 / 278	315 LB-FT 180 %	475 LB-FT 268 %	48

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS / HOUR	APPROX. MOTOR WGT
68 dBA	78 dBA	25 LB-FT^2	- LB-FT^2	20 SEC.	2	1075 LBS.

***** SUPPLEMENTAL INFORMATION *****

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	BLUE (ENAMEL)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	ODE						
BALL	BALL	POLYREX EM	T	NONE	NONE	AISI 1045 (C-240)	CAST IRON
6314	6313						

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

*

N

O

T

E

S

INVERTER TORQUE: CONSTANT 20:1

INV. HP SPEED RANGE: NONE

ENCODER: NONE

NONE NONE

NONE NONE PPR

BRAKE: NONE NONE

NONE P/N NONE


NONE NONE

NONE FT-LB NONE V NONE Hz



LEESON ELECTRIC CORPORATION

TYPICAL PERFORMANCE CURVE for AC MOTOR

Model No 199029.00Curve at 460
60
40Volts
HZ
HPHP 40&30PHASE 3VOLTS 230/460&190/380Catalog No 199029.00HZ 60&50RPM 1188&990

Torque in Lb.Ft

FL TORQUE 177 Lb.Ft
 BD TORQUE 475.0 Lb.Ft
 LR TORQUE 315 Lb.Ft

FL AMPS 94/47
 PU TORQUE 282.0 Lb.Ft
 LR AMPS 278

WINDING CHT36460001-1

Date 11/13/2018