

PRODUCT INFORMATION PACKET



Model No: 199037.00
Catalog No: 199037.00
REPLACED BY 365TTFCD6036



Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E






Nameplate Specifications

Phase	3	Output HP	75 & 60 Hp
Output KW	56.0 & 45.0 kW	Voltage	230/460 & 190/380 V
Speed	1782 & 1480 rpm	Service Factor	1.15 & 1.15
Frame	365T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	95.4 & 95 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	173/86.5 & 166/83 A	Power Factor	85
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Drive End Bearing Size	6314	Opp Drive End Bearing Size	6313
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	4	Rotation	Reversible
Resistance Main	.091 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Inverter Load	CONSTANT 2:1		
Outline Drawing	B-SS620115	Connection Drawing	A-EE7308AA-LE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/22/2023




<DIMENSIONS IN TABLE ARE CONSIDERED REFFERENCE>

364T	36.61	18.50	11.25	7.99
365T	38.39	20.28	12.25	8.88
FRAME	C	B	2F	BS

<MAY NOT BE DRAWN TO SCALE>

				TOLERANCES UNLESS SPECIFIED		 REGAL-BELOIT CORPORATION	DRA		
				DEC.	INCHES		CHK		
				X	±.1		APP		
				XX	±.03	TITLE OUTLINE 364/365T FR. - TEFC - CAST IRON	SCA		
K	CORRECTED DESCRIPTION ECO-0112150	WGJ 10/31/16	EH	XXX	±.005		REF		
1	ADDED 'BS' DIM. PER. ECO-0048910	RFH04/07/2014	EH	XXXX	±.0005	MAT'L.	FMP		
NO.	REVISION	BY & DATE	CHK	ANG	±1/2	FINISH	PRE		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP		CAD FILE	SS620115	SIZE	DRAWING NO.
				DIST				B	SS62





CERTIFICATION DATA SHEET

1051 CHEYENNE AVE.
GRAFTON, WI 53024
PH. 262-377-8810

CONN. DIAGRAM: A-EE7308AA-LE

CATALOG #: 199037.00

OUTLINE: B-SS620115

MOUNTING: F1/F2 CAPABLE

WINDING #: CHT36540003 1

TYPICAL MOTOR PERFORMANCE DATA

HP	kW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
75&60	56.0&45.0	1800	1782&1480	365T	TEFC	G	B

PH	Hz	VOLTS	AMPS	START TYPE	DUTY	INSL	S.F.	AMB°C
3	60/50	230/460&190/380	173/86.5&166/83	LINE OR INVERTER	CONTINUOUS	F1	1.15/1.15	40

FULL LOAD EFF:	95.4&95	3/4 LOAD EFF:	95.4	1/2 LOAD EFF:	95	GTD. EFF	ELEC. TYPE
FULL LOAD PF:	85&85	3/4 LOAD PF:	84	1/2 LOAD PF:	78	95	SQ CAGE INV RATED

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B,D. TORQUE	F.L. RISE°C
221 LB-FT	1060 / 530	460 LB-FT 208 %	550 LB-FT 248 %	75

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS / HOUR	APPROX. MOTOR WGT
75 dBA	85 dBA	20.5 LB-FT^2	- LB-FT^2	20 SEC.	2	1100 LBS.

*** SUPPLEMENTAL INFORMATION ***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	BLUE (ENAMEL)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	ODE						
BALL	BALL	POLYREX EM	T	NONE	NONE	AISI 1045 (C-240)	CAST IRON
6314	6313						

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

*

N

O

T

E

S

INVERTER TORQUE: CONSTANT 2:1

INV. HP SPEED RANGE: NONE

ENCODER: NONE

NONE NONE

NONE NONE PPR

BRAKE: NONE NONE

NONE P/N NONE


NONE NONE

NONE FT-LB NONE V NONE Hz



LEESON ELECTRIC CORPORATION

TYPICAL PERFORMANCE CURVE for AC MOTOR

Model No 199037.00Curve at 460
60
75Volts
HZ
HPHP 75&60PHASE 3VOLTS 230/460&190/380Catalog No 199037.00HZ 60&50RPM 1782&1480

Torque in Lb.Ft

FL TORQUE 221 Lb.Ft
 BD TORQUE 550.0 Lb.Ft
 LR TORQUE 460 Lb.Ft

FL AMPS 173/86.5
 PU TORQUE 400.0 Lb.Ft
 LR AMPS 530

WINDING CHT36540003-1

Date 11/13/2018