



### Nameplate Specifications

|                        |                     |                            |                             |
|------------------------|---------------------|----------------------------|-----------------------------|
| Phase                  | 3                   | Output HP                  | 75 & 60 Hp                  |
| Output KW              | 56.0 & 45.0 kW      | Voltage                    | 230/460 & 190/380 V         |
| Speed                  | 3572 & 2972 rpm     | Service Factor             | 1.15 & 1.15                 |
| Frame                  | 365TS               | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection       | Efficiency                 | 94.1 & 94.1 %               |
| Ambient Temperature    | 40 °C               | Frequency                  | 60 & 50 Hz                  |
| Current                | 167/83.5 & 160/80 A | Power Factor               | 89                          |
| Duty                   | Continuous          | Insulation Class           | F                           |
| Design Code            | B                   | KVA Code                   | G                           |
| Drive End Bearing Size | 6312                | Opp Drive End Bearing Size | 6312                        |
| UL                     | Recognized          | CSA                        | Y                           |
| CE                     | N                   | IP Code                    | 43                          |
| Number of Speeds       | 1                   |                            |                             |

### Technical Specifications

|                       |                              |                       |                  |
|-----------------------|------------------------------|-----------------------|------------------|
| Electrical Type       | Squirrel Cage Inverter Rated | Starting Method       | Line Or Inverter |
| Poles                 | 2                            | Rotation              | Reversible       |
| Resistance Main       | .07 Ohms                     | Mounting              | Rigid Base       |
| Motor Orientation     | Horizontal                   | Drive End Bearing     | Ball             |
| Opp Drive End Bearing | Ball                         | Frame Material        | Cast Iron        |
| Shaft Type            | TS                           | Assembly/Box Mounting | F1/F2 CAPABLE    |
| Inverter Load         | CONSTANT 2:1                 |                       |                  |
| Outline Drawing       | SS620284-365TS               | Connection Drawing    | A-EE7308AA-LE    |