

PRODUCT INFORMATION PACKET



Model No: 199071.00

Catalog No: 199071.00

SOLETE REPLACED BY B199071.00 ..60HP..3600RPM.364TSC.TEFC.230/460V.3PH.60HZ.CONT.40C.1.15SF.RIGI
-C.....GENERAL PURPOSE.....



Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications


Phase	3	Output HP	60 & 50 Hp
Output KW	45.0 & 37.0 kW	Voltage	230/460 & 190/380 V
Speed	3575 & 2975 rpm	Service Factor	1.15 & 1.0
Frame	364TSC	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	93.6 & 93.6 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	135/67.5 & 133/66.5 A	Power Factor	88.5
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	H
Drive End Bearing Size	6312	Opp Drive End Bearing Size	6312
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	2	Rotation	Reversible
Resistance Main	.0677 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	TS	Assembly/Box Mounting	F1/F2 CAPABLE
Inverter Load	CONSTANT 20:1		
Outline Drawing	SS620303-364TSC	Connection Drawing	A-EE7308AA-LE


This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/22/2023

SS620303



364TSC	34.48	18.50	11.25
365TSC	36.26	20.28	12.25
FRAME	C	B	2F

TOLERANCES UNLESS SPECIFIED		DEC. INCHES		REGAL-BELOIT CORPORATION		DRAWN SY 4-21-2010	
.X			$\pm .1$			CHK	HZJ 4-21-2010
.XX			$\pm .03$			APPD	CL 4-21-2010
.XXX			$\pm .005$			SCALE	1=8
.XXXX			$\pm .0005$			REF	
						FMF	HWADA
						PREV	
NO.	REVISION	BY & DATE	CHK	ANG	$\pm 1/2$	FINISH	
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT						RFP	
						DIST	
						CAD FILE	SS620303
						SIZE	DRAWING NO.
						B	SS620303
						REV.	



DRAWING REVISION C		REVISION BY D.FROEHLICH	DATE 02-09-2015	TOLERANCES UNLESS OTHERWISE SPECIFIED: DEC. INCH mm ANGLE .X ±0.1 [±2.5] ±7° 30" .XX ±0.02 [±0.51] .XXX ±0.005 [±0.127] .XXXX ±0.0005 [±0.0127] REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [0.076/.381] CORNER FILLETS: .02 [0.51] MACHINED SURFACES: 200 INCH ✓ mm ✓ mm SHOWN IN [BRACKETS]	DRAWN BY HV	REGAL Regal Beloit America, Inc.		
ECO ECO-0070906		APPROVED BY MG	DATE 02-09-2015		DATE 06-08-20152	DESCRIPTION CONN DIAGRAM-EXTERNAL 3 PHASE - 2/1 DELTA - 12 LEADS		
ECO DESCRIPTION UPDATED IEC CONNECTIONS					APPROVED BY DR			
COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.					DATE 06-11-2012	MATERIAL		PROCESS/FINISH
					REFERENCE	SIZE A		DRAWING NUMBER EE7308AA-LE
				THIRD ANGLE PROJECTION				



CERTIFICATION DATA SHEET

1051 CHEYENNE AVE.
GRAFTON, WI 53024
PH. 262-377-8810

CONN. DIAGRAM: A-EE7308AA-LE

CATALOG #: 199071.00

OUTLINE: B-SS620303

MOUNTING: F1/F2 CAPABLE

WINDING #: CHT36420001 1

TYPICAL MOTOR PERFORMANCE DATA

HP	kW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
60&50	45.0&37.0	3600	3575&2975	364TSC	TEFC	H	B

PH	Hz	VOLTS	AMPS	START TYPE	DUTY	INSL	S.F.	AMB°C
3	60/50	230/460&190/380	135/67.5&133/66.5	LINE OR INVERTER	CONTINUOUS	F1	1.15/1.0	40

FULL LOAD EFF:	93.6&93.6	3/4 LOAD EFF:	93.6	1/2 LOAD EFF:	91.7	GTD. EFF	ELEC. TYPE
FULL LOAD PF:	88.5&89.5	3/4 LOAD PF:	86.5	1/2 LOAD PF:	81	93	SQ CAGE INV RATED

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
88 LB-FT	950 / 475	185 LB-FT 210 %	245 LB-FT 278 %	55

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS / HOUR	APPROX. MOTOR WGT
75 dBA	85 dBA	8.5 LB-FT^2	40 LB-FT^2	20 SEC.	2	1000 LBS.

*** SUPPLEMENTAL INFORMATION ***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
C-FACE	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	BLUE (ENAMEL)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	ODE						
BALL	BALL	POLYREX EM	TS	NONE	NONE	AISI 1045 (C-240)	CAST IRON
6312	6312						

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

*

N

O

T

E

S

INVERTER TORQUE: CONSTANT 20:1

INV. HP SPEED RANGE: NONE

ENCODER: NONE

NONE NONE

NONE NONE PPR

BRAKE: NONE NONE


NONE P/N NONE

NONE NONE

NONE FT-LB NONE V NONE Hz

Model No 199071.00Catalog No 199071.00
LEESON ELECTRIC CORPORATION
 TYPICAL PERFORMANCE CURVE for AC MOTOR

 Curve at 460
60
60

 Volts
 HZ
 HP
HP 60&50PHASE 3VOLTS 230/460&190/380HZ 60&50RPM 3575&2975

Torque in Lb.Ft

 FL TORQUE 88 Lb.Ft
 BD TORQUE 245.0 Lb.Ft
 LR TORQUE 185 Lb.Ft

 FL AMPS 135/67.5
 PU TORQUE 150.0 Lb.Ft
 LR AMPS 475

WINDING CHT36420001-1

Date 12/13/2018