

PRODUCT INFORMATION PACKET



Model No: 199097.00

Catalog No: 199097.00

Close-Coupled Pump Motor, 5 & 3 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 3600 & 3000 RPM,
182JP Frame, DP



Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications



Phase	3	Output HP	5 & 3 Hp
Output KW	3.7 & 2.2 kW	Voltage	230/460 & 190/380 V
Speed	3460 & 2915 rpm	Service Factor	1.15 & 1.15
Frame	182JP	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	87.5 & 88.5 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	12.4/6.2 & 9/4.5 A	Power Factor	88
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	H
Drive End Bearing Size	6307	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
IP Code	22	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	2	Rotation	Reversible
Resistance Main	3.05 Ohms	Mounting	Rigid Base
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	JP
Overall Length	20.46 in	Frame Length	6.73 in
Shaft Diameter	0.875 in	Shaft Extension	7.28 in
Assembly/Box Mounting	F1 ONLY		
Connection Drawing	EE7308	Outline Drawing	SS620859-182JP

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/21/2023

SS620859



182JP	12.09	19.44
184JP	13.11	20.46
FRAME	B1	B

			TOLERANCES UNLESS SPECIFIED		REGAL-BELOIT CORPORATION		DRAWN WY 5-9-2017	
			DEC.	INCHES			CHK ZXW 5-9-2017	
			.X	±.1			APPD ZYH 5-9-2017	
			.XX	±.03	TITLE		SCALE 1=4	
			.XXX	±.005	ODP-182/184JP FR-ROLLED STEEL		REF	
A	RELEASED FOR PRODUCTION	ECD-0093138	WGJ 09-06-17	EMH .XXXX	±.0005	MAT'L.	FMF Wuxi	
NO.	REVISION		BY & DATE	CHK ANG	±1/2	FINISH	PREV	
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP	CAD FILE	SS620859	SIZE B	DRAWING NO. SS620859
				DIST				REV. A



				TOLERANCES UNLESS SPECIFIED		 Regal Beloit America, Inc.	DRAWN RM 11/20/1990				
5	CHG TO REGAL LOGO	SL 09/10/2015	AB	DEC.	INCHES		CHK ML 11/21/1990				
4	REVISED IEC NOTATIONS	MSG 11/15/2011	CMN	.X	±.1		APPD SAS 04/24/2003				
3	ADDED IEC NOTATIONS... (U1), (V1) ETC. MU95194	MSG 5/10/2010	MJS	.XX	±.02		SCALE 1=1				
2	ADDED THE OPTIONAL CORD CONNECTION MU46318	RDH 04/24/2003	DRS	.XXX	±.005	TITLE CONNECTION DIAGRAM 3ø – DUAL VOLTAGE MOTOR	REF				
1	REDRAWN	RM 11/20/1990		.XXXX	±.0005	MAT'L	FMF				
NO.	REVISION	BY & DATE	CHK	ANG	±7"30"	FINISH	PREV				
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT			RFP		CAD FILE ee7308		SIZE	DRAWING NO.	PAGE	OF	REV.
			DIST WP				A	EE7308			5

Data Sheet

Date: 2/1/2018

199097.00



Data @ 460 V

Motor Load Data


Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	2.40	2.60	3.6	4.8	5.9	6.8	7.5	38.0	
Torque (ft-lb)	0.00	1.80	3.7	5.6	7.6	8.8	9.6	17.0	
RPM	3600	3570	3538	3502	3495	3,475	3450	0	
Efficiency (%)		84.0	86.5	87.5	86.5	86.5	85.5		
P.F. (%)	7.0	52.0	74.0	84.0	90.0	90.0	90.0	61.0	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	1800	2675	3495	3600
Current (Amps)	38.0	34.0	28.0	5.9	2.40
Torque (ft-lb)	17.0	15.0	22.5	7.6	0.00

Information Block

HP	5.0			
Sync. RPM	3600			
Frame	182			
Enclosure	DP			
Construction	TDB			
Voltage	230/460#190/380	V		
Frequency	60	Hz		
Design	B			
LR Code letter	H			
Service Factor	1.15			
Temp Rise @ FL	55	° C		
Duty	CONT			
Ambient	40	° C		
Elevation	1,000	feet		
Rotor/Shaft wk²	0.20	Lb-Ft²		
Ref Wdg	CHT18220006 NONE			
Sound Pressure @ 1M	55	dBA		
VFD Rating	VARIABLE 10:1			
Outline Dwg	SS620570			
Conn. Diag	EE7308			
Additional Specifications:				
0				
0				
EQUIV CKT (OHMS / PHASE)				
R1	R2	X1	X2	Xm
1.8140	1.3040	4.4510	1.9850	163.5800



Speed - Torque Curve

