



Nameplate Specifications

| | | | |
|------------------------|---------------------|----------------------------|---------------------|
| Phase | 3 | Output HP | 10 & 7.50 Hp |
| Output KW | 7.5 & 5.6 kW | Voltage | 230/460 & 190/380 V |
| Speed | 1770 & 1475 rpm | Service Factor | 1.15 & 1.15 |
| Frame | 215TC | Enclosure | Drip Proof |
| Thermal Protection | No Protection | Efficiency | 91.7 & 91.7 % |
| Ambient Temperature | 40 °C | Frequency | 60 & 50 Hz |
| Current | 25.6/12.8 & 24/12 A | Power Factor | 79 |
| Duty | Continuous | Insulation Class | F |
| Design Code | B | KVA Code | G |
| Drive End Bearing Size | 6307 | Opp Drive End Bearing Size | 6206 |
| UL | Recognized | CSA | N |
| CE | Y | IP Code | 22 |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|------------------------------|-----------------------|------------------|
| Electrical Type | Squirrel Cage Inverter Rated | Starting Method | Line Or Inverter |
| Poles | 4 | Rotation | Reversible |
| Resistance Main | .805 Ohms | Mounting | Rigid Base |
| Motor Orientation | Horizontal | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | T | Assembly/Box Mounting | F1/F2 CAPABLE |
| Inverter Load | VARIABLE 10:1 | | |
| Outline Drawing | SS620657 | Connection Drawing | EE7308-LE |