

PRODUCT INFORMATION PACKET

marathon®
Motors

Model No: 213TTFW6001

Catalog No: E2015

XRI® General Purpose General Purpose Motor, 7.50 & 7.50 HP, 3 Ph, 60 & 50 Hz, 230/460 & 200/400 V,
3600 & 3000 RPM, 213TC Frame, TEFC



Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord

Nameplate Specifications


Phase	3	Output HP	7.50 & 7.50 Hp
Output KW	5.6 & 5.6 kW	Voltage	230/460 & 200/400 V
Speed	3540 & 2940 rpm	Service Factor	1.15 & 1.0
Frame	213TC	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	90.2 & 89.5 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	17.8/8.9 & 20.4/10.2 A	Power Factor	87
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	H
Drive End Bearing Size	6309	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		

Technical Specifications


Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	2	Rotation	Reversible
Resistance Main	1.163 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Overall Length	20.97 in
Frame Length	11.15 in	Shaft Diameter	1.375 in
Shaft Extension	3.12 in	Assembly/Box Mounting	F3
Outline Drawing	A-SS88794-1115	Connection Drawing	A-EE7308

DASH	FR.	C	AG	BS
965	213T	19.47	16.35	5.43
1115	213/15T	20.97	17.85	6.93
1240	213/15T	22.22	19.10	8.18

SS88794



NOTES:
1. NAMEPLATE READ FROM LOCATION AT "C".

				TOLERANCES UNLESS SPECIFIED		<div> Regal Beloit America, Inc.</div>				DRAWN TAT 08-13-2004				
				DEC.	INCHES					CHK ML 08-13-2004				
				.X	±.1					APPD TB 08-13-2004				
				.XX	±.03					SCALE 1=5				
				.XXX	±.005	TITLE OUTLINE – F3 C'BOX MOUNTING 210T FR. –BB–TS–TEFC–R/S – C'FACE				REF				
1	TITLE BLOCK LOGO CHANGE PER ECO-0078542		MDV 06/09/2015	.XXXX	±.0005					MAT'L.				FMF
NO.	REVISION		BY & DATE	CHK	ANG	± 7'30"	FINISH				PREV			
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT				RFP			CAD FILE ss88794			SIZE A	DRAWING NO. PAGE OF		REV. 1	
				DIST LB							SS88794			



NO.	REVISION	BY & DATE	CHK	ANG	TOLERANCES UNLESS SPECIFIED		RFP	CAD FILE	SIZE	DRAWING NO.	PAGE	OF	REV.
					DEC.	INCHES							
5	CHG TO REGAL LOGO	SL 09/10/2015	AB		DEC.	INCHES							
4	REVISED IEC NOTATIONS	MSG 11/15/2011	CMN	.X	±.1								
3	ADDED IEC NOTATIONS... (U1), (V1) ETC. MU95194	MSG 5/10/2010	MJS	.XX	±.02								
2	ADDED THE OPTIONAL CORD CONNECTION MU46318	RDH 04/24/2003	DRS	.XXX	±.005								
1	REDRAWN	RM 11/20/1990		.XXXX	±.0005								
					±7'30"								
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT								CAD FILE ee7308	A	EE7308			5

CERTIFICATION DATA SHEET

Model#: 213TTFW6001 BP
 CONN. DIAGRAM: A-EE7308
 OUTLINE: A-SS88794-1115

WINDING#: K213269 R3 1
 ASSEMBLY: F3

TYPICAL MOTOR PERFORMANCE DATA

HP	KW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
7 1/2 & 7 1/2	5.6 & 5.6	3600	3540 & 2940	213TC	TEFC	H	B

PH	Hz	VOLTS	FL AMPS	START TYPE	DUTY	INSL	S.F	AMB°C	ELEVATION
3	60/50	230/460#200/ 400	17.8/8.9 & 20.4/ 10.2	LINE OR INVERTER	CONTINUOU S	F4	1.15/1.0	40	3300

FULL LOAD EFF: 90.2 & 89.5	3/4 LOAD EFF: 89.5	1/2 LOAD EFF: 86.5	GTD. EFF	ELEC. TYPE	NO LOAD AMPS
FULL LOAD PF: 87 & 87	3/4 LOAD PF: 83	1/2 LOAD PF: 74.5	89.5	SQ CAGE INV RATED	6 / 3

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
11.1 LB-FT	127 / 63.5	24 LB-FT 216	38 LB-FT 342	40

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS /HOUR	APPROX. MOTOR WGT
72 dBA	82 dBA	0.55 LB-FT^2	12 LB-FT^2	15 SEC.	2	140 LBS.

*** SUPPLEMENTAL INFORMATION ***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
C-FACE	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	BLUE (ENAMEL)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	OPE						
BALL	BALL						
6309	6206	POLYREX EM	T	NONE	NONE	AISI 1045 (C-240)	ROLLED STEEL

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE /n HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

If Inverter equals NONE, contact factory for further
information

INVERTER TORQUE: CONSTANT 10:1		
INV. HP SPEED RANGE: 1.5 X BASE SPEED		
ENCODER: NONE		
NONE NONE		
NONE NONE PPR		
BRAKE: NONE NONE		
NONE P/N NONE		
NONE NONE		
- FT-LB	NONE V	NONE Hz

*
N
O
T
E
S
*

DATE: 06/22/2017 05:57:16 AM
 FORM 3531 REV.3 02/07/99
 ** Subject to change without notice.

Data Sheet

Date: 6/29/2017

Customer: _____

Attention: _____

Submitted by: FAREEDA DUDEKULA



213TTFW6001

Submittal

Data @ 460 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	3.0	4.0	5.0	7.0	8.9	10.0	11.0	63.5	
Torque (ft-lb)	0.00	2.50	5.5	8.5	11.1	12.5	14.0	24.0	
RPM	3600	3585	3575	3560	3540	3,535	3530	0	
Efficiency (%)		80.0	86.5	89.5	90.2	90.2	89.5		
P.F. (%)	9.0	54.0	74.5	83.0	87.0	88.0	89.0	40.0	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle	Information Block				
Speed (RPM)	0	1800	3250	3540	3600	HP	7.5			
Current (Amps)	63.5	57.0	40.0	8.9	3.0	Sync. RPM	3600			
Torque (ft-lb)	24.0	22.0	38.0	11.1	0.00	Frame	213			
<div><div>— Efficiency (%) — P.F. (%) — Current (Amps)</div><div>EFFICIENCY, P.F., AND CURRENT VS. LOAD</div></div>						Enclosure	TEFC			
						Construction	TFW			
						Voltage	30/460#200/40V			
						Frequency	60 Hz			
						Design	A			
						LR Code letter	H			
						Service Factor	1.15			
						Temp Rise @ FL	40 ° C			
						Duty	CONT			
						Ambient	40 ° C			
						Elevation	1,000 feet			
						Rotor/Shaft wk ²	0.55 Lb-Fl ²			
						Ref Wdg	K213269 R3			
						Sound Pressure @ 1M	72 dBA			
						VFD Rating	CONSTANT 10:1			
						Outline Dwg	A-SS88794-1115			
						Conn. Diag	A-EE7308			
Additional Specifications:										
0										
0										
EQUIV CKT (OHMS / PHASE)										
R1		R2		X1		X2		Xm		
0.6880		0.4690		2.2980		2.3930		80.8920		

Speed -Torque Curve

