

### Nameplate Specifications

|                        |                  |                            |                             |
|------------------------|------------------|----------------------------|-----------------------------|
| Phase                  | 3                | Output HP                  | 3 & 3 Hp                    |
| Output KW              | 2.2 & 2.2 kW     | Voltage                    | 230/460 & 200/400 V         |
| Speed                  | 1170 & 970 rpm   | Service Factor             | 1.15 & 1.0                  |
| Frame                  | 213TC            | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection    | Efficiency                 | 89.5 & 87.5 %               |
| Ambient Temperature    | 40 °C            | Frequency                  | 60 & 50 Hz                  |
| Current                | 8.8/4.4 & 10/5 A | Power Factor               | 70                          |
| Duty                   | Continuous       | Insulation Class           | F                           |
| Design Code            | B                | KVA Code                   | K                           |
| Drive End Bearing Size | 6309             | Opp Drive End Bearing Size | 6206                        |
| UL                     | Recognized       | CSA                        | Y                           |
| CE                     | Y                | IP Code                    | 43                          |
| Number of Speeds       | 1                |                            |                             |

### Technical Specifications

|                       |                              |                       |                  |
|-----------------------|------------------------------|-----------------------|------------------|
| Electrical Type       | Squirrel Cage Inverter Rated | Starting Method       | Line Or Inverter |
| Poles                 | 6                            | Rotation              | Reversible       |
| Resistance Main       | 2.785 Ohms                   | Mounting              | Rigid Base       |
| Motor Orientation     | Horizontal                   | Drive End Bearing     | Ball             |
| Opp Drive End Bearing | Ball                         | Frame Material        | Rolled Steel     |
| Shaft Type            | T                            | Overall Length        | 19.47 in         |
| Frame Length          | 9.65 in                      | Shaft Diameter        | 1.375 in         |
| Shaft Extension       | 3.12 in                      | Assembly/Box Mounting | F3               |
| Outline Drawing       | A-SS88794-965                | Connection Drawing    | A-EE7308         |