

### Nameplate Specifications

Output HP	2.0/.25 Hp	Output KW	1.5 kW
Frequency	60 Hz	Voltage	230 V
Current	SF 10.0/2.1 A	Speed	3450/1725 rpm
Service Factor	1.2	Phase	1
Duty	Continuous	Insulation Class	F
Frame	Y56J	Enclosure	Drip Proof
Thermal Protection	Thermally Protected	Ambient Temperature	50 °C
UL	Recognized	CSA	Y
Number of Speeds	2-2-VT		

### Technical Specifications

Electrical Type	Psc Low Speed, Cap Start/Cap Run High Speed	Poles	2/4
Rotation	Clockwise	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	7/16 Threaded	Overall Length	13.55 in
Frame Length	8.25 in	Shaft Diameter	0.625 in
Shaft Extension	2.604 in		
Connection Drawing	D0000026-001.PCX	Outline Drawing	B2979-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2022