



Nameplate Specifications

Phase	1	Output HP	10 & 15 Hp
Output KW	7.5 & 11.2 kW	Voltage	230 & 230 V
Speed	3520 & 3455 rpm	Service Factor	1.5 & 1.0
Frame	215TZ	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	85.5 & 85.5 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	39.5 & 61.5 A	Power Factor	82
Duty	Continuous	Insulation Class	F
Design Code	L	KVA Code	G
Drive End Bearing Size	6307	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	N	IP Code	12
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	2	Rotation	Selective Counterclockwise
Resistance Main	.113 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Overall Length	20.42 in
Frame Length	12.40 in	Shaft Diameter	1.125 in
Shaft Extension	4.59 in	Assembly/Box Mounting	F3
Outline Drawing	A-SS87934-1240	Connection Drawing	A-EE9048PH